

# Leather Anti Fatigue Eye Mask

皮革抗疲勞眼罩

Model : MS-MA

## Features:

- Imported heating material, 3 second safe heating technology
- Micro atomization steam; 3D surround steam hot compress
- Both sides of the ear are made of 100% silk, with upgraded design
- Adjustable button, transparent PVC button, can be used to adjust the size
- Promote eye blood circulation, improve dark circles, relieve eye fatigue
- 進口發熱材料，3秒安全發熱技術
- 微米級霧化蒸汽；3D環繞蒸汽熱敷
- 耳部兩側採用100%真絲拼接，設計感升級
- 可調節按扣，透明PVC扣子，可用來調節使用大小
- 促進眼部血液迴圈，改善黑眼圈，緩解眼疲勞



## Specifications

Product Model 產品型號	MS-MA
Product Material 產品材質	PVC leather PVC皮革
Power 功率	2.5W-4.5W
Color 顏色	indigo blue 靛青藍
Rated voltage 額定電壓	5V
Gear position pattern 檔位 模式	three gears, timing three gears for temperature adjustment 三檔定時三檔調溫
Packing size 包裝尺寸	23.7*8.2*4cm
Package weight 包裝重量	140g

## Instructions

- 1.用溫控線將眼罩與電源設備連接
- 2.單擊開關按鈕可開啟加熱功能，默認紅色高檔
- 3.再次單擊調整檔位（紅色高檔、綠色中檔、藍色低檔）
- 4.長按2秒開啟定時功能，定時30分鐘（開啟時燈閃爍）

### 注意事項

- 1) 產品不使用時，請及時關閉電源，避免長時間加熱
- 2) 建議斷開電源5分鐘後再拿開眼罩，使眼睛適應光線和溫度變化
- 3) 洗滌時切忌用力搓，也不要擰絞，只要用手擠壓除去水分，然後陰涼處曬乾即可，請勿機洗
- 4) 請存放於乾燥陰涼處，避免暴曬、受潮
- 5) 眼睛如患有疾病或損傷，請在醫生指導下使用
- 6) 內含發熱材料，使用時和使用後有溫度狀態下，不得折疊
- 7) 本品不是玩具，請置於幼兒無法觸及之處；除非監護人已事先對其進行設置，或已就其使用方法給予充分指導。